

Leica KL Quick Configuration Guide


Leica KL1500LCD

31150201 \$599

Spare bulb


15V/150W (EFR)

31153000 \$22



Daylight filter

31158306 \$20



Leica KL2500LCD

31250201 \$1045

Spare bulb


24V/250W (ELC)

31253000 \$26



Daylight filter (28mm)

31258306 \$29




Continuous ringlight

31157410 \$414

Achro + Plan 58mm obj.

31157420 \$443


Plan + PlanApo 66mm obj.



8x1000mm bundle

TL bases, Coax, NV

31155401 \$260



Dual rigid gooseneck

4.5x600mm


31154202 \$221



Focusing lens w/o filter

10446391 \$31 ea.

Leica KL2500 LCD Fluorescence Configuration Guide



Leica KL2500LCD

31250201 \$1045

Spare bulb


24V/250W (ELC)

31253000 \$26

Filter slide housing for M-series

Both housing and filter holder included

10447158 \$1165



Yellow filter -
For use w/
Blue excitation
filter

Red filter - For
use w/ Green
excitation
filter

OR




Barrier filters (square)

Yellow (515LP) - 35000166 \$60

Red (610LP) - 35000165 \$60

15x1000mm flexible bundle


31250102 \$378



**Holder - 15mm
light guide**

31157430 \$73

OR




**Articulated arm for column
clamp**

Remove 1 black clamp to interface 31157430

Locktite required

10399211 \$224



Articulated arm

31158345 \$150



Base for articulated arm

31158340 \$58

Excitation filters (28mm)

Blue (460/60) - 31258313 \$309

OR

Green (545/50) - 31258314 \$223



**Column clamp for
M-series**

10445654 \$61

AND